

Product Info Sheet: FLOWMAT Paddle Flow Switch # 228-FLOWMAT

The FLOMAT paddle flow switch is equipped with a timer delay to allow the pump to start, adjustable from 0-10 seconds, with a test button

When power is supplied to the FLOMAT the Control Relay pulls which allows the pump to start immediately. If after the time set the flow is not greater than 201/m the FLOMAT will turn the pump off.


It will also turn off should the flow stop at any later period.


The electrical components are housed in a separate enclosure to the paddle mechanism and are activated by a magnet located in the head of the paddle, which is made of glass reinforced Polyamide

The paddle can be trimmed to operate in various pipe sizes from 1" to 4"

Specifications:

- Min Flo 20 l/min
- Max Pressure 10Bar
- Max Temp 100 deg C
- Supply Voltage 230vac or 24vac
- Relay Contact Rating 10(4)A 250vac







www.argondistributors.co.nz